

Model # UVC 3024

99.9% sterilizing rate

Model # UVC 3024

Sterilization mode: ultraviolet C

Wavelength: 200-280nm UV Radiation Type: UV C Bulb shape: Tube

Battery type: Rechargeable



How to setup:

Step 1: Charge the UV Light Lamp before first use "RED light" Means charging and "green light" full charged.

Step 2: Press on the power ON/OFF for 3 seconds you will hear 3 beeps And unit will turn ON.

Step 3: Auto stop time active in 5 minutes you hear a been and unit Turn OFF.

Step 4: You can manually turn it off by pressing the ON/OFF button.

<u>Benefits</u>

Wavelength https://uvcanada.ca

- Smart motion sensor activated when toilet
 lid up
- Fast acting and efficient 99.9% sterilization
- Eliminate a variety of Pathogens
- Sterilization without use of harmful chemicals that leave residue.
- Built In Rechargeable batteries and USB charging
- Light weight and easy to transport
- Ozone-Free

The ez

Guide

Suggestions

 Disinfect mobile phone, keys, masks, jewelry, watches, socks, headphones, toothbrushes makeup brushes, remotes bedding/mattress, kitchen utensils, personal hygiene items, counters, bathroom fixtures, office desk computers keyboards, retail shops can use to disinfect display counters & amp; merchandise

Caution and Warnings

- Do not directly look at UV light when sanitization is in progress.
- Avoid exposure to UV rays, it can be harmful to the eyes and skin
- This equipment is intended for indoor use only
- Do not alter the device.
- Do not use this Lamp for other than its intended purpose, as described in suggestions
- · Equipment should be protected from the elements and from temperatures below freezing
- Do not operate the UV Lamp if any damage to the unit is visible or suspected.

Maintenance

Keep the UV Sterilizer clean you can gentle wipe it with soft cloth

Copyright© ez technology Canada 2020